

Reikan FoCal Fully Automatic Test Report

for D7100 (serial number 4341964) with 150-600mm f/5-6.3

Test run on: 19/01/2016 03:49:14 with FoCal 2.0.6.2416W

Report created on: 19/01/2016 03:57:44 with FoCal 2.0.6W

Overview

Test Information

Property	Description
Data Creation FoCal Version	2.0.6.2416W
Data Analysis FoCal Version	2.0.6W
OS Version	Microsoft Windows NT 6.2.9200.0
Source Mode	Camera Mode
Image Capture Mode	JPEG
Analysis Method	Multi-ESH (RGB)
Camera Model	D7100
Firmware Version	V1.02
Serial Number	4341964
Shutter count (start)	14696
Test Colour Temp	3200 K
Lens	150-600mm f/5-6.3
Focal Length	240,0mm
Termination Reason	Success
Test Aperture	f/8,0
Test ISO	100
Defocus Method	Defocus away from the camera
Distance to Target	2,9m
Starting AF Fine Tune	0
AF Consistency Constraint	6%
Shot Count	23
Calculated AF Fine Tune	-4
Result Confidence	Good
Consistency of Focus	99,7%

User Notes

mire 133 mm
lampe Q1250
sac accroché au trépied carbone 055CXPro4 et tête pendulaire


Test Details

Lens Profile Chart

The Lens Profile chart shows how the image quality changes as the AF Microadjustment changes. The orange line represents how the sharpness is expected to change through all values, so the highest point on this line corresponds to the best predicted AF Microadjustment value.

Each point on the chart represents the result of a single shot:


- Red marker: unoptimised sharpness
- Green marker: optimised sharpness
- Orange circle within marker - this is the representative sharpness for this AFMA
- Orange curve - the predicted sharpness across the AFMA range
- Green triangle - highest value
- Red triangle - lowest value



Before/After Comparison

The images show the before and after shots.


	AF Fine Tune
Before	0
After	-4



RGB Analysis Chart

The RGB Analysis chart shows the predicted sharpness across the AF Microadjustment range for red, green and blue light. The vertical lines indicate the predicted best AF Microadjustment for each of the 3 colours.

It is important to note that when run in JPEG mode, there is some contamination between the colours so the result is not truly representative.



RGB Analysis Details

Property	Description
Red:	
Red Result	-4
Red Confidence	Good
Green:	
Green Result	-3
Green Confidence	Good
Blue:	
Blue Result	-6
Blue Confidence	Good

AF Fine Tune: -20


The following table shows information obtained for this test point:

	Shot 1	Shot 2	Shot 3
Aperture	f/8,0	f/8,0	f/8,0
Shutter Speed	1/320s	1/320s	1/320s
EV	14,3	14,3	14,3
Colour Temperature	Unknown	Unknown	Unknown
Camera Temperature	Unknown	Unknown	Unknown
Quality Measure	1201,6	1312,2	1211,5
Optimised	No	No	No
Ignored	No	No	No
Spectral Power (R/G/B)	31/33/36	31/33/36	32/33/36
Red Quality	1159,0	1263,2	1167,1
Green Quality	1151,1	1259,2	1161,6
Blue Quality	1284,1	1399,9	1288,7
HVR	-1,0%	-1,8%	-1,5%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:



AF Fine Tune: -14


The following table shows information obtained for this test point:

	Shot 1	Shot 2
Aperture	f/8,0	f/8,0
Shutter Speed	1/320s	1/320s
EV	14,3	14,3
Colour Temperature	Unknown	Unknown
Camera Temperature	Unknown	Unknown
Quality Measure	1663,9	1766,0
Optimised	No	No
Ignored	No	No
Spectral Power (R/G/B)	31/33/36	31/33/36
Red Quality	1619,5	1719,3
Green Quality	1640,8	1756,3
Blue Quality	1725,0	1815,7
HVR	-0,8%	0,2%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:




AF Fine Tune: -10


The following table shows information obtained for this test point:

	Shot 1	Shot 2
Aperture	f/8,0	f/8,0
Shutter Speed	1/320s	1/320s
EV	14,3	14,3
Colour Temperature	Unknown	Unknown
Camera Temperature	Unknown	Unknown
Quality Measure	1931,3	1935,3
Optimised	No	No
Ignored	No	No
Spectral Power (R/G/B)	31/33/36	31/33/36
Red Quality	1863,2	1897,0
Green Quality	1960,1	1973,6
Blue Quality	1966,7	1940,8
HVR	-0,3%	-0,6%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:




AF Fine Tune: -9


The following table shows information obtained for this test point:

	Shot 1	Shot 2
Aperture	f/8,0	f/8,0
Shutter Speed	1/320s	1/320s
EV	14,3	14,3
Colour Temperature	Unknown	Unknown
Camera Temperature	Unknown	Unknown
Quality Measure	1980,8	1998,8
Optimised	No	No
Ignored	No	No
Spectral Power (R/G/B)	32/33/36	32/33/36
Red Quality	1932,5	1932,4
Green Quality	2032,2	2046,4
Blue Quality	1978,4	2015,6
HVR	-0,1%	-0,2%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:




AF Fine Tune: -4


The following table shows information obtained for this test point:

	Shot 1	Shot 2
Aperture	f/8,0	f/8,0
Shutter Speed	1/250s	1/250s
EV	13,9	13,9
Colour Temperature	Unknown	Unknown
Camera Temperature	Unknown	Unknown
Quality Measure	2029,7	2030,0
Optimised	No	No
Ignored	No	No
Spectral Power (R/G/B)	32/32/36	32/32/36
Red Quality	1990,3	1982,6
Green Quality	2155,9	2130,4
Blue Quality	1953,2	1981,2
HVR	-0,9%	-0,5%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:




AF Fine Tune: 0


The following table shows information obtained for this test point:

	Shot 1	Shot 2
Aperture	f/8,0	f/8,0
Shutter Speed	1/320s	1/320s
EV	14,3	14,3
Colour Temperature	Unknown	Unknown
Camera Temperature	Unknown	Unknown
Quality Measure	1971,2	1984,9
Optimised	No	No
Ignored	No	No
Spectral Power (R/G/B)	31/32/37	31/32/37
Red Quality	1965,4	1970,6
Green Quality	2134,5	2145,9
Blue Quality	1838,2	1860,3
HVR	-1,2%	-0,7%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:



AF Fine Tune: 1


The following table shows information obtained for this test point:

	Shot 1	Shot 2
Aperture	f/8,0	f/8,0
Shutter Speed	1/250s	1/250s
EV	13,9	13,9
Colour Temperature	Unknown	Unknown
Camera Temperature	Unknown	Unknown
Quality Measure	1949,8	1969,3
Optimised	No	No
Ignored	No	No
Spectral Power (R/G/B)	32/32/36	32/32/36
Red Quality	1950,3	1959,0
Green Quality	2104,1	2117,9
Blue Quality	1817,5	1859,7
HVR	-0,6%	-1,8%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:



AF Fine Tune: 6


The following table shows information obtained for this test point:

	Shot 1	Shot 2	Shot 3
Aperture	f/8,0	f/8,0	f/8,0
Shutter Speed	1/250s	1/250s	1/250s
EV	13,9	13,9	13,9
Colour Temperature	Unknown	Unknown	Unknown
Camera Temperature	Unknown	Unknown	Unknown
Quality Measure	1570,5	1771,0	1664,0
Optimised	No	No	No
Ignored	No	No	No
Spectral Power (R/G/B)	32/32/36	32/32/36	31/32/37
Red Quality	1553,2	1757,7	1653,5
Green Quality	1736,0	1948,0	1828,4
Blue Quality	1439,9	1641,0	1527,2
HVR	-2,3%	-1,7%	-2,7%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:



AF Fine Tune: 10


The following table shows information obtained for this test point:

	Shot 1	Shot 2	Shot 3
Aperture	f/8,0	f/8,0	f/8,0
Shutter Speed	1/320s	1/320s	1/320s
EV	14,3	14,3	14,3
Colour Temperature	Unknown	Unknown	Unknown
Camera Temperature	Unknown	Unknown	Unknown
Quality Measure	1252,6	1374,7	1438,7
Optimised	No	No	No
Ignored	No	No	No
Spectral Power (R/G/B)	31/32/37	31/32/37	31/32/37
Red Quality	1241,5	1365,5	1424,0
Green Quality	1348,9	1499,9	1584,1
Blue Quality	1177,1	1273,5	1323,1
HVR	-4,7%	-5,5%	-3,3%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:




AF Fine Tune: 20


The following table shows information obtained for this test point:

	Shot 1	Shot 2
Aperture	f/8,0	f/8,0
Shutter Speed	1/320s	1/320s
EV	14,3	14,3
Colour Temperature	Unknown	Unknown
Camera Temperature	Unknown	Unknown
Quality Measure	951,2	975,6
Optimised	No	No
Ignored	No	No
Spectral Power (R/G/B)	31/32/37	31/32/36
Red Quality	928,6	960,1
Green Quality	953,6	1004,8
Blue Quality	969,6	965,8
HVR	-1,5%	-2,9%

The following image is a crop of the section of image analysed by FoCal:



The following image is a crop of the section of image analysed by FoCal:




Lens Profile

The Lens Profile chart shows how the image quality changes as the AF Microadjustment changes. The orange line represents how the sharpness is expected to change through all values, so the highest point on this line corresponds to the best predicted AF Microadjustment value.

Each point on the chart represents the result of a single shot:

- Red marker: unoptimised sharpness
- Green marker: optimised sharpness
- Orange circle within marker - this is the representative sharpness for this AFMA
- Orange curve - the predicted sharpness across the AFMA range
- Green triangle - highest value
- Red triangle - lowest value




Focus Consistency

The Focus Consistency chart shows the focus variability at each tested point where available. This is calculated from the spread in sharpness values from shots at a single AF Microadjustment value.

A value of 100% indicated perfect repeatability. In normal use, a values above 97% indicate acceptable autofocus repeatability, and above 99% indicate very good repeatability. Note that the consistency of focus measurement is less relevant far from the best AF Microadjustment value.

If FoCal Comparison Data is available for this camera and lens a red/blue/green overlay will be added to indicate how your camera and lens performance compares with other users as follows:

- Red: indicates below-average performance,
- Blue: typical performance experienced by other users
- Green: above average performance.




Astigmatism Factor

The Astigmatism Factor chart shows the image quality ratio between the horizontal and vertical analysis directions. If this value varies by more than 10% across the range, or the average value is more than $\pm 5\%$ then your lens may be suffering from some decentering or lens element alignment issues.

If FoCal Comparison Data is available for this camera and lens a red/blue/green overlay will be added to indicate how your camera and lens performance compares with other users as follows:

- Red: indicates below-average performance,
- Blue: typical performance experienced by other users
- Green: above average performance.



Result Convergence

The Result Convergence chart indicates how FoCal determined the best AF Microadjustment value as more points were added to the data. There is no result for the first few points, then the result should stabilise as more points are added towards the end of the test (the right side of the chart).

The size of the green area gives an indication of the confidence in the result at that point. A large green area spreading across many AF Microadjustment values indicates poor data that will not give an acceptable final result.




Image Motion

As changes are made inside a lens (e.g. focussing or aperture change), the image projected onto the sensor can move slightly. The Image Motion chart shows the absolute number of pixels moved for each image compared to the first image captured.

Typically, the Image Motion should be significantly less than 10 pixels, and a repeatable higher value could indicate misaligned lens optics, camera movement or vibration during the test or other environmental or lens issues.

If FoCal Comparison Data is available for this camera and lens a red/blue/green overlay will be added to indicate how your camera and lens performance compares with other users as follows:

- Red: indicates below-average performance,
- Blue: typical performance experienced by other users
- Green: above average performance.

